# VZWSMART-SFK1 | TIE BACK ASSEMBLY



#### TIF BACK ASSEMBLY

Tieback Bracket / Stiff Arm, 2-3/8" OD x 10 ft Pipe with Attachment Hardware, for 1-1/2" to 8-5/8" OD or 8" 60 degree angle or 6" 90 degree angle tower leg

#### **Product Classification**

**Product Type** Stiff arm mount

Ordering Note ANDREW® non-standard product

#### General Specifications

**Mounting** Round and angle legs

Pipe, quantity 1

#### **Dimensions**

Pipe Length3,048 mm | 120 inMounting Diameter, maximum203.2 mm | 8 inMounting Diameter, minimum38.1 mm | 1.5 inPipe Outer Diameter60.325 mm | 2.375 in

## Material Specifications

Material Type Hot dip galvanized steel

## Packaging and Weights

Included Attachment hardware | Pipe

Packaging quantity 1

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

ANDREW®
an Amphenol company

# VZWSMART-SFK1 | TIE BACK ASSEMBLY



#### Included Products

SA-B - Stiff Arm /Tieback Brackets for 2-3/8 in OD pipe - Pipe not included





## Stiff Arm / Tieback Brackets for 2-3/8 in OD pipe - Pipe not included

#### **Product Classification**

**Product Type** Stiff arm mount

#### General Specifications

**Mounting** Round and angle legs

Pipe, quantity 0

#### Dimensions

 Height
 6 in | 152.4 mm

 Width
 8 in | 203.2 mm

 Length
 8 in | 203.2 mm

 Mounting Diameter, maximum
 3.5 in | 88.9 mm

 Mounting Diameter, minimum
 1.9 in | 48.26 mm

### Material Specifications

Material Type Hot dip galvanized steel

## Packaging and Weights

Included Attachment hardware | Brackets

Packaging quantity 1

**Weight, net** 18.3 lb | 8.301 kg

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



# SA-B

