

SHK-2937-3-P



Single Hanger Kit for 29 to 37mm cable, triple stack; includes hardware and angle adapter

Product Classification

Product Type	Hanger kit
Product Brand	ValuSite™
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	3
Color	Black
Hanger Type	Composite clamp
Mounting	M8 hardware

Dimensions

Maximum Stack Height	3
Height	35.6 mm 1.402 in
Width	91.4 mm 3.598 in
Length	302.3 mm 11.902 in
Compatible Cable Diameter Range	29–37 mm
Compatible Diameter, maximum	37.1 mm 1.461 in
Compatible Diameter, minimum	29 mm 1.142 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Mechanical Specifications

SHK-2937-3-P

Vibration Survival

≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation

≥500 hours in salt spray chamber

Environmental Strength Capability

Double cable weight

UV Resistance, minimum with no degradation

≥1000 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed

20 cm | 7.874 in

Width, packed

20 cm | 7.874 in

Length, packed

35 cm | 13.78 in

Included

Angle adapter | Hardware

Packaging quantity

10

Weight, gross

4.71 kg | 10.384 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power