


3

| | PART NO. | DESCRIPTION | PIPE BUNDLE |
|---|-----------------|--|-------------|
| A | MC-PK14M-B | MC-PK14M-B LOW PROFILE PLATFORM 15"-50" | |
| | MC-PK14M-12-96 | LOW PROFILE PLATFORM 15"-50" 12 96 PIPE | MT-651-96 |
| | MC-PK14M-12-126 | LOW PROFILE PLATFORM 15"-50" 12 126 PIPE | MT-537 |

4

| | REVISIONS | | |
|------|---|--|---|
| REV. | DESCRIPTION | DATE | APPROVED |
| А | INITIAL RELEASE | DRR 26AUG16 | 8000015873 |
| В | UPDATED SNUB NOSE WELDMENT AND PIPE MOUNT PLATE | MRC 17MAR20 | BCAMPBELLCON 8000039693 |
| С | UPDATED BOM STRUCTURE. MC-AF-1100-00 WAS MCPK14M01; MT546174120 WAS MT- 547-174 | JL1183 11NOV22 | BA1025 40160588CMO |
| | A B | REV. DESCRIPTION A INITIAL RELEASE B UPDATED SNUB NOSE WELDMENT AND PIPE MOUNT PLATE C UPDATED BOM STRUCTURE. MC-AF-1100-00 WAS MCPK14M01; MT546174120 WAS MT- | REV.DESCRIPTIONDATEAINITIAL RELEASEDRR 26AUG16BUPDATED SNUB NOSE WELDMENT AND PIPE MOUNT PLATEMRC 17MAR20CUPDATED BOM STRUCTURE. MC-AF-1100-00 WAS MCPK14M01; MT546174120 WAS MT- 11NOV22JL1183 11NOV22 |



В

D

С




D


С

 $\neg >$


В



DETAIL A SCALE 1 : 6




DETAIL B SCALE 1 : 5




DETAIL C SCALE 1 : 5

COMPONENT PART NUMBERS PROVIDED FOR ASSEMBLY PURPOSES; INDIVIDUAL COMPONENTS MAY BE SHIPPED AS PARTS WITHIN AN INCLUDED KIT.

| | ITEM | PART NO. | DESCRIPTION | QTY. | NOTE |
|---|------|---------------|--|------|-------------------|
| A | 1 | MC-RM1550-3 | 15" - 50" OD RINGMOUNT | 1 | |
| | 2 | MC-AF-1100-00 | WELDMENT, CO-LOCATION PLATFORM | 3 | |
| | 3 | GUB-4355 | 1/2" X 3-5/8" X 5" GALV U-BOLT | 12 | |
| | 4 | GB-0524A | 5/8" X 2-1/2" GALV BOLT KIT (A325) | 12 | |
| | 5 | MT546174120 | 2.88" OD X 174" LONG PIPE | 3 | |
| | 6 | MT-219S-H | SADDLE PIPE MOUNTING KIT 2-3/7"X2-7/8"OD | 12 | NO FOR MC-PK14M-B |
| | 7 | MT-651-96 | 2.375" OD X 96" PIPE | 12 | SEE TABLE1 |
| 0 | | | 4 | | |



| NTENNA PIPE |
|-------------|
| - |
| MT-651-96 |
| MT-537 |
| |



3

3

