

F042MMS1



FlexTwist® Flexible Twist for WR42, 17.7–26.5 GHz, with interface types UBR220 and UBR220, 300 mm

Product Classification

Product Type	Rectangular waveguide, flexible twist
Product Brand	FlexTwist®

General Specifications

Component	Flexible Twist
Interface	UBR220
Interface 2	UBR220

Dimensions

Length	300 mm 11.811 in
Waveguide Size	WR42 WG20 R220

Electrical Specifications

Attenuation	2.62 dB/m 0.799 dB/ft
Average Power	100 W
Operating Frequency Band	17.7 – 26.5 GHz
Peak Power	39 kW
VSWR	1.2

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)	38 mm 1.496 in
Minimum Bend Radius, Multiple Bends (H Plane)	76 mm 2.992 in
Maximum Twist	510 °/m 155.448 °/ft
Pressurization, maximum	0.31 N/mm ² 45 psi

Regulatory Compliance/Certifications

F042MMS1

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS

Classification

Above maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant/Exempted

Compliant/Exempted

