



M4800 LC-Duplex Adapter, Black (24 ea/pkg)

Product Classification

Regional Availability	Asia Europe Latin America
Portfolio	CommScope®
Product Type	Adapter kit

General Specifications

Color	Black
--------------	-------

Dimensions

Height	17.78 mm 0.7 in
Width	18.542 mm 0.73 in
Depth	8.382 mm 0.33 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic
----------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0

Packaging and Weights

Packaging quantity	24
---------------------------	----

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

760253195 | M4800 LCD-Adapter-24

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

