

760254043 | EPX-1U-CHD-OPEN-FX



EPX 1U open fixed panel, accepts (8) CHD style modules, adapter packs, or splice cassettes, providing up to 48 duplex LC ports

Product Classification

Regional Availability	Asia Australia/New Zealand China
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	EPX

General Specifications

Application	Accepts eight CHD modular cassettes
Color	Black
Intelligence Type	Not iPatch® ready
Interface, front	Unloaded
Module/Adapter Pack Slots, quantity	4
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Fixed
Total Fibers, quantity	96

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	327.91 mm 12.91 in

Packaging and Weights

Packaging quantity	1
Weight, net	1.057 kg 2.33 lb