MC-K10L-6-72



Monopole Co-location T-Frame Kit, 30 in to 60 in OD, 10 ft face, includes pipe

OBSOLETE

This product was discontinued on: August 18, 2022

Replaced By:

MC-K10M-6-72 Monopole Co-location T-Frame kit, 12 in to 50 in OD, 10 ft 6 in face, includes pipe

Product Classification

Product TypeMonopole T-frame kit

General Specifications

Mounting Monopole, 762–1524 mm (30–60 in) OD

Pipe, quantity 6
Sectors, quantity 3

Dimensions

 Height
 1,828.8 mm | 72 in

 Face Width
 3.2 m | 10.5 ft

 Width
 3,200.4 mm | 126 in

 Length
 914.4 mm | 36 in

 Pipe Length
 1,828.8 mm | 72 in

 Mounting Diameter, maximum
 1524 mm | 60 in

 Mounting Diameter, minimum
 762 mm | 30 in


 Pipe Outer Diameter
 60.96 mm | 2.4 in

 Stand-off Distance
 914.4 mm | 36 in



MC-K10L-6-72

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 150 ft AGL | 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC

Wind Rating Criteria Four 72 in x 8 in panel antennas per sector

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Cellular pipe frames | Pipe mounts | Ring mount | Stand-off arms

Packaging quantity 1

Weight, net 466.792 kg | 1,029.1 lb

an Amphenol company

Page 2 of 10

MC-K10L-6-72

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

MC-K10L-B – Monopole Co-location T-Frame Kit, 30 in to 60 in OD, 10 ft face, pipe ordered

separately


MT-219-H – Pipe Mount Kit - 2-3/8" TO 3-1/2" PIPE - pipe not included MT-651 – Plain End Pipe, 2-3/8 in OD x 72 in .120" A500C 46Ksi

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code



MC-K10L-B



Monopole Co-location T-Frame Kit, 30 in to 60 in OD, 10 ft face, pipe ordered separately

Product Classification

Product Type Monopole T-frame kit

General Specifications

Mounting Monopole, 762–1524 mm (30–60 in) OD

762 mm | 30 in

Pipe, quantity 0
Sectors, quantity 3

Mounting Diameter, minimum

Dimensions

 Height
 254 mm | 10 in

 Face Width
 3.2 m | 10.5 ft

Width 3,200.4 mm | 126 in

Length 914.4 mm | 36 in


Mounting Diameter, maximum 1524 mm | 60 in

Pipe Outer Diameter 60.96 mm | 2.4 in

Stand-off Distance 914.4 mm | 36 in

MC-K10L-B

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 150 ft AGL | 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC

Wind Rating Criteria Four 72 in x 8 in panel antennas per sector

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Cellular pipe frames | Ring mount | Stand-off arms

Packaging quantity 1

Weight, net 376.89 kg | 830.9 lb

ANDDEW

an Amphenol company

MC-K10L-B

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code



MT-219-H



Pipe Mount Kit - 2-3/8" TO 3-1/2" PIPE - pipe not included

Product Classification

Product Type Pipe mount kit

General Specifications

Mounting Pipe, 60.3 mm (2-3/8 in) OD | Pipe, 88.9 mm (3-1/2 in) OD

Dimensions

 Height
 254 mm | 10 in

 Width
 127 mm | 5 in

 Length
 127 mm | 5 in

 Mounting Diameter, maximum
 88.9 mm | 3.5 in

Mounting Diameter, minimum 60.325 mm | 2.375 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Crossover bracket | U-bolts

Packaging quantity 1

Weight, net 4.9 kg | 10.803 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



MT-219-H





Plain End Pipe, 2-3/8 in OD x 72 in .120" A500C 46Ksi

Product Classification

Product Type Plain end pipe

General Specifications

Pipe, quantity 1

Dimensions

 Height
 60.96 mm | 2.4 in

 Width
 60.96 mm | 2.4 in

 Length
 1,828.8 mm | 72 in

 Pipe Length
 1,828.8 mm | 72 in

 Pipe Outer Diameter
 60.96 mm | 2.4 in

 Material Thickness
 3.048 mm | 0.12 in

Material Specifications

Material Type A500 | Hot dip galvanized steel

Material Grade C

Material Strength 46 KSI

Packaging and Weights

Included Pipe **Packaging quantity** 1

Weight, net 8 kg | 17.637 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ANDREW® an Amphenol company

MT-651

ROHS UK-ROHS Compliant/Exempted
Compliant/Exempted



