

# MTC9076M69M96



T-Arm Monopole Mount, Includes Ring Mount for 15"-50" OD Monopole, 6.5 ft face plus (9) 2-7/8" OD x 96" Antenna Pipes and Corner Tiebacks

## Product Classification

**Product Type** Monopole T-frame kit

## General Specifications

**Mounting** Monopole, 381–1270 mm (15–50 in) OD  
**Pipe, quantity** 9  
**Sectors, quantity** 3

## Dimensions

**Height** 2,438.4 mm | 96 in  
**Face Width** 1.981 m | 6.5 ft  
**Width** 2,133.6 mm | 84 in  
**Pipe Length** 2,438.4 mm | 96 in  
**Mounting Diameter, maximum** 1270 mm | 50 in  
**Mounting Diameter, minimum** 381 mm | 15 in  
**Pipe Outer Diameter** 73.025 mm | 2.875 in  
**Stand-off Distance** 1,010.412 mm | 39.78 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** For Specifications, please contact your local ANDREW representative  
**Wind Rating Test Method** TIA/EIA-222-G

## Packaging and Weights

**Included** Pipe mounts | Plain end pipes | Ring mount | Stand-off arms  
**Packaging quantity** 1

# MTC9076M69M96

---

**Weight, net** 574.702 kg | 1267 lb

\* Footnotes

**Wind Rating** BWS—Base Wind Speed; FBC—Florida Building Code