# MC-K14L-B



Monopole Co-location T-Frame Kit, 30 in to 60 in OD, 14 ft face, pipe ordered separately

#### OBSOLETE

This product was discontinued on: August 18, 2022		
Replaced By:		
MC-K14M-B	Monopole Co-location T-Frame kit, 12 in to 50 in OD, 14 ft 6 in face, pipe ordered separately	


#### Product Classification

Product Type	Monopole T-frame kit			
General Specifications				
Mounting	Monopole, 762–1524 mm (30–60 in) OD			
Pipe, quantity	0			
Sectors, quantity	3			
Dimensions				
Height	254 mm   10 in			
Face Width	4.42 m   14.5 ft			
Width	4,419.6 mm   174 in			
Length	914.4 mm   36 in			
Mounting Diameter, maximum	1524 mm   60 in			
Mounting Diameter, minimum	762 mm   30 in			
Pipe Outer Diameter	60.96 mm   2.4 in			
Stand-off Distance	914.4 mm   36 in			



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

## Outline Drawing



### Material Specifications

Material Type

Hot dip galvanized steel

#### Mechanical Specifications

Wind Rating	120 mph (BWS) at 150 ft AGL   140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC	
Wind Rating Criteria	Four 72 in x 8 in panel antennas per sector	
Wind Rating Test Method	TIA/EIA-222	

#### Packaging and Weights

Included	Cellular pipe frames   Ring mount   Stand-off arms
Packaging quantity	1
Weight, net	431.684 kg   951.7 lb

Page 2 of 3



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

# MC-K14L-B

### Regulatory Compliance/Certifications

#### Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

#### Included Products

- MC-RM3060-3 Universal Ring Mount, 30 in to 60 in OD
- MT-197 Single Support Arm, 36 in, includes pipe
- MT-216-14NS Cellular Pipe Frame, 14 ft face

#### \* Footnotes

Wind Rating BWS-Base Wind Speed; FBC-Florida Building Code

