## 760254443 | FMS-K2BI-L0M4-48-SP



FMS Panel, 1U, 19 in, black, Includes 24 x LC OM4 Duplex Adaptors (48F), 48 x OM4 LC Pigtails 48 x Splice protectors. Splice trays (2) and cable glands

## **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | India

Portfolio CommScope®

**Product Type** Fiber patch/splice panel

Product Series FMS

General Specifications

Functionality Patching | Splicing

**Body Style** Symmetrical

Cable Exit Location Rear, left side | Rear, right side

ColorBlackInterface, frontLC/UPCFiber Color CodeTIA-598Rack TypeEIA 19 in

Rack Units 1

**Shelf Movement** Sliding

Splice Trays Included, quantity 2

**Splicing Type** Heat shrink, single fiber fusion

Total Ports, quantity 48

**Dimensions** 

 Height
 44.45 mm | 1.75 in

 Width
 482.6 mm | 19 in

 Depth
 320 mm | 12.598 in

Material Specifications

**Finish** Powder coated

**COMMSCOPE®** 

## 760254443 | FMS-K2BI-L0M4-48-SP

Material Type Steel

Optical Specifications

**Fiber Mode** Multimode

 Fiber Type
 OM4

 Insertion Loss, maximum
 0.3 dB

 Return Loss, minimum
 27 dB

Packaging and Weights

**Included** Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

