NG4-VSMLF28



NG4access® Module VAM, Splitter, 1x8, symmetrical split, singlemode, LC /APC, front, left, 2 circuits

- VAMs help enhance optical transport systems by providing flexible, easy to incorporate optical components into the network
- VAMs increase fiber capacity and help troubleshooting or distributing signals to multiple subscribers
- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | EMEA | India | Latin

America | North America

PortfolioCommScope®Product TypeSplitter moduleProduct BrandNG4access®Product SeriesFACT | NG4

Government RequirementsBuild America Buy America (BABA) compliant*

General Specifications

Device Type Plug-and-play module

Functionality Splitting

Technology Type Planar lightwave circuit (PLC)

Access Front

Application For use with NG4 access frames

Distribution Type 1 x 8 splitter (2)

Interface, frontLC/APCInterface, InputLC/APCInterface, OutputLC/APC

Location of Manufacturing Waived per BABA waiver for BEAD Program

Split Ratio Symmetrical

Splitter, quantity 2

COMMSCOPE®

NG4-VSMLF28

Tray Orientation Left orientation

Dimensions

 Height
 13.21 mm | 0.52 in

 Width
 159.77 mm | 6.29 in

 Depth
 130.3 mm | 5.13 in

Optical Specifications

Directivity, minimum 55 dB

Performance Grade Grade O (PLC, low loss)

Polarization Dependent Loss, maximum 0.2 dB Uniformity, maximum 1.4 dB

Wavelength Range 1260–1625 nm

Insertion Loss, Splitter, maximum10.8 dBReturn Loss, Connector, minimum55 dB

Packaging and Weights

Packaging quantity 1