

MC-PK8-B



Low-Profile Co-location Platform Base Face Kit, 8 ft face, 15 in to 38 in OD, No Pipes or Support Rail

Product Classification

Product Type Monopole platform kit

General Specifications

Mounting Monopole, 381–965 mm (15–38 in) OD
Pipe, quantity 0
Sectors, quantity 3

Dimensions

Height 254 mm | 10 in
Face Width 2.438 m | 8 ft
Width 2,438.4 mm | 96 in
Length 914.4 mm | 36 in
Face Support Pipe Diameter 88.9 mm | 3.5 in
Mounting Diameter, maximum 965.2 mm | 38 in
Mounting Diameter, minimum 304.8 mm | 12 in
Pipe Outer Diameter 0 mm | 0 in
Stand-off Distance 914.4 mm | 36 in
Mounting Circumference, maximum 962.66 mm | in
Mounting Circumference, minimum 378.46 mm | in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Criteria Four 72 in x 12 in panel antennas per sector
Wind Rating Test Method TIA/EIA-222

MC-PK8-B

Packaging and Weights

Included	Platform Ring mount
Packaging quantity	1
Weight, net	360.107 kg 793.9 lb