

MCG21HD-12M-9-126



G21HD High Capacity 3-Sector Monopole Frame, 12.5 ft 2.88 in OD face pipes, includes nine 126 in pipes; For patents, see www.cs-pat.com.

OBSOLETE

This product was discontinued on: July 29, 2022

Replaced By:

MCG22HD-12M-12-126	G22HD High Capacity 3-Sector Monopole Frame with 2 7/8in OD x 12.5ft face. Includes twelve 2 3/8in OD x 126in antenna pipes
--------------------	---

Product Classification

Product Type	High capacity monopole sector frame
---------------------	-------------------------------------

General Specifications

Mounting Monopole, 381–1270 mm (15–50 in) OD

Pipe, quantity	9
----------------	---

Sectors, quantity	3
--------------------------	---

Dimensions

Height 3,200.4 mm | 126 in

Face Width 3.81 m | 12.5 ft

Width 3,810 mm | 150 in

Pipe Length 3,200.4 mm | 126 in

Face Support Pipe Diameter 73.025 mm | 2.875 in

Mounting Diameter, maximum	1270 mm		50 in
-----------------------------------	---------	--	-------

Mounting Diameter, minimum	381 mm 15 in
-----------------------------------	----------------

Pipe Outer Diameter	60.325 mm 2.375 in
----------------------------	----------------------

Stand-off Distance 1,125.22 mm | 44.3 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

MCG21HD-12M-9-126

Mechanical Specifications

Wind Rating	For Specifications, please contact steelproducts@commscope.com or call 800-255-1479
Wind Rating Test Method	TIA/EIA-222

Packaging and Weights

Included	Pipe mounts Plain end pipes (9) Ring mounts (2) Sector frames (3) Stiff arm
Packaging quantity	1
Weight, net	644.101 kg 1420 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--