# MCG22-14M-9-96



G22 High Capacity 3-Sector Monopole Frame, 14 ft 6 in face, includes nine 96 in pipes; For patents, see www.cs-pat.com.

#### **OBSOLETE**

This product was discontinued on: July 29, 2022 Replaced By:

MCG22HDX-14M-12-96 G22HDX High Capacity 3-Sector Monopole Frame with 2 7/8in OD x 14.5ft face. Includes twelve 2 7 /8in OD x 96in antenna pipes

### Product Classification

**Product Type** High capacity monopole sector frame

General Specifications

**Mounting** Monopole, 381–1270 mm (15–50 in) OD

Pipe, quantity 9
Sectors, quantity 3

Dimensions

**Height** 2,438.4 mm | 96 in

Face Width  $4.42 \, \mathrm{m} \, \mid \, 14.5 \, \mathrm{ft}$ 

**Width** 4,419.6 mm | 174 in

**Pipe Length** 2,438.4 mm | 96 in

**Face Support Pipe Diameter** 60.325 mm | 2.375 in

**Mounting Diameter, maximum** 1270 mm | 50 in


Mounting Diameter, minimum 381 mm | 15 in

**Pipe Outer Diameter** 60.325 mm | 2.375 in

Stand-off Distance 1,117.6 mm | 44 in

## Outline Drawing





Material Specifications

Material Type

Hot dip galvanized steel

Mechanical Specifications

**Load Capacity** 

With additional stiff arm at 300 ft AGL: 600 lb per pipe w/out ice / 1275 lb per pipe including ice

Page 2 of 3



# MCG22-14M-9-96

**Wind Rating** For Specifications, please contact your local ANDREW representative

Wind Rating Test Method TIA/EIA-222

Wind Rating with Additional Stiff Arm 300 ft AGL: 120 mph (BWS) without ice /60 mph with ice

Packaging and Weights

Included Pipe mounts | Plain end pipes (9) | Ring mounts (2) | Sector frames

(3) | Stiff arm

Packaging quantity

**Weight, net** 878.155 kg | 1936 lb

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



### \* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

Wind Rating with Additional Stiff Arm BWS—Base Wind Speed; FBC—Florida Building Code

