

# TW-18N

---

Torque Wrench for coupling torque of Type N connectors, 18mm opening



## Product Classification

<b>Product Type</b>	Wrench
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Application</b>	Torques Type N connectors
<b>Calibration</b>	6 mo
<b>Tool Type</b>	Torque wrench

## Dimensions

<b>Wrench Opening</b>	18 mm   0.709 in
-----------------------	------------------

## Material Specifications

<b>Material Type</b>	Steel
----------------------	-------

## Mechanical Specifications

<b>Torque Tolerance</b>	-5/+0
<b>Torque Value</b>	20 in lb   2.26 N-m

## Packaging and Weights

<b>Height, packed</b>	256.54 mm   10.1 in
<b>Width, packed</b>	88.9 mm   3.5 in
<b>Length, packed</b>	88.9 mm   3.5 in
<b>Packaging quantity</b>	1

# TW-18N

---

**Weight, gross** 0.33 kg | 0.728 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

