

760254924 | M4800A-1U-GS-WH



M4800 1U Angled Modular Panel, 48 port (MGS600 / MGS400 / UNJ10GT / UNJ10G / UNJ600 / UNJ500), White

- Available for use with the DYMO® labeling solution

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	RJ45 patch panel
Product Brand	GigaSPEED X10D®
Product Series	M Series

General Specifications

ANSI/TIA Category	6 6A
Color	White
Intelligence Type	Passive
Panel Style	Angled
Rack Type	EIA 19 in
Rack Units	1

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	143 mm 5.63 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic Steel
----------------------	-----------------------------------------------------

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing

760254924 | M4800A-1U-GS-WH

Flammability Rating UL 94 V-0

Safety Standard UL | cUL

Packaging and Weights

Packaging Material Eco-friendly, single-use plastics-free

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

