760252937 | OTE200-08MH-18-S12-B-P



Mini-OTE 200-Series, Optical Terminal Enclosure, 8-port full-size connector, 1x8 PLC splitter, black, pole mount

- Optical Terminal Enclosures incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Functionality to splice and store feeder cable in the field with the possibility to splice in the field two extra branch cables
- Hardened adapters are factory-terminated and environmentally sealed to ensure rapid plug-and play drop cable installations
- Integrated external cable fixation guarantees easy, fast and reliable cable manipulations

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America

Product Type Access terminal, with splitter

Product Series Mini-OTE 200

General Specifications

Cable Sealing TypeCompressed gel

Cable Type No cable (stubless)

Distribution Type 1 x 8 splitter

Drop Port TypeHardened full-size SC/APC

Drop Port, quantity 8

Enclosure Color Black

Mounting Handhole | Pole | Wall

Split Ratio Symmetrical

Splitter, quantity 1

Stub Type No stub

Dimensions

Height 358.5 mm | 14.114 in

Width 166 mm | 6.535 in


Depth 129.3 mm | 5.091 in


Cable Length, stub 0 ft (0 m)


Dimension Drawing

COMMSC PE°


760252937 | OTE200-08MH-18-S12-B-P







Ordering Tree



Material Specifications

Enclosure Material TypeGlass filled polypropylene (GF-PP)

Optical Specifications

Fiber Type G.657.A2

Operating Wavelength Range 1260 – 1635 nm

Attenuation Single Ports, typical 10.8 dB

COMMSC PE°

760252937 | OTE200-08MH-18-S12-B-P

Return Loss, Single Ports, minimum 55 dB

Environmental Specifications

Operating Temperature $-40 \, ^{\circ}\text{C} \text{ to } +65 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F to } +149 \, ^{\circ}\text{F})$

Relative Humidity 5%–100%, condensing

Environmental Space Above ground | Below ground | Buried

Qualification Standards IEC 60529, IP68 + 2 m waterhead

UV Resistance UV stabilized

Packaging and Weights

Included Cable termination unit (2) | Enclosure (1) | Fiber pigtail cassette (1) | Splice

Cassette (2)

Packaging quantity 1

Packaging Type Box | Carton

Weight, net 1.77 kg | 3.902 lb

Included Products

CW8094-002 - TENIO™ Cable Termination Unit kit

TENIO-CTU-L-(10)

CW8094-002 | TENIO-CTU-L-(10)



TENIO™ Cable Termination Unit kit

Product Classification

Regional Availability EMEA

Product Type Cable termination kit

Product Series TENIO

Environmental Specifications

Environmental Space Outdoor

Packaging and Weights

Packaging quantity

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

