# MT-220-120



#### Pipe Mount Kit, 2-3/8 in OD x 126 in

#### **Product Classification**

**Product Type** Pipe mount kit

## General Specifications

**Mounting** Pipe, 88.9 mm (3-1/2 in) OD

Pipe, quantity 1

#### **Dimensions**

**Height** 3,200.4 mm | 126 in

 Width
 127 mm | 5 in

 Length
 127 mm | 5 in

 Pipe Length
 3,200.4 mm | 126 in

 Pipe Outer Diameter
 60.96 mm | 2.4 in

# Material Specifications

Material Type Hot dip galvanized steel

# Packaging and Weights

Included Crossover bracket | Plain end pipes | U-bolts

Packaging quantity 1

**Weight, net** 22.1 kg | 48.722 lb

# Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

#### Included Products

MT-219-H – Pipe Mount Kit - 2-3/8" TO 3-1/2" PIPE - pipe not

ANDREW® an Amphenol company

# MT-220-120

included

MT-537

- Plain End Pipe, 2-3/8 in OD x 126 in .120" A500C 46Ksi

# MT-219-H



#### Pipe Mount Kit - 2-3/8" TO 3-1/2" PIPE - pipe not included

#### **Product Classification**

**Product Type** Pipe mount kit

General Specifications

**Mounting** Pipe, 60.3 mm (2-3/8 in ) OD | Pipe, 88.9 mm (3-1/2 in) OD

**Dimensions** 

 Height
 254 mm | 10 in

 Width
 127 mm | 5 in

 Length
 127 mm | 5 in

 Mounting Diameter, maximum
 88.9 mm | 3.5 in

**Mounting Diameter, minimum** 60.325 mm | 2.375 in

Material Specifications

Material Type Hot dip galvanized steel

# Packaging and Weights

Included Crossover bracket | U-bolts

Packaging quantity 1

**Weight, net** 4.9 kg | 10.803 lb

## Regulatory Compliance/Certifications

# Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



# MT-219-H





#### Plain End Pipe, 2-3/8 in OD x 126 in .120" A500C 46Ksi

A500 46 ksi steel

#### **Product Classification**

Product Type Plain end pipe

#### General Specifications

Pipe, quantity 1

#### **Dimensions**

 Height
 60.96 mm | 2.4 in

 Width
 60.96 mm | 2.4 in

 Length
 3,200.4 mm | 126 in

 Pipe Length
 3,200.4 mm | 126 in

 Pipe Outer Diameter
 60.325 mm | 2.375 in

 Material Thickness
 3.048 mm | 0.12 in

# Material Specifications

Material Type A500 | Hot dip galvanized steel

Material Grade C

Material Strength 46 KSI

# Packaging and Weights

Included Pipe
Packaging quantity 1

**Weight, net** 18 kg | 39.683 lb

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Page 5 of 6



# MT-537

ROHS UK-ROHS Compliant/Exempted
Compliant/Exempted



