760254767 | C-004-CN-5K-M04BK/28G/GY/E



Indoor/Outdoor Low Smoke Zero Halogen, LazrSPEED® Central Loose Tube Fiber Optic Cable, 4-fiber, Multimode OM4, Gel-filled, black. Provides Rodent Resistance.

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series C-CN

General Specifications

Cable TypeLoose tubeSubunit TypeGel-filledJacket ColorBlackJacket MarkingMetersJacket Marking MethodInkjet

Jacket Marking Text COMMSCOPE GB OPTICAL CABLE 760254767 INT/EXT RODENT RESIST

GLT 4X50/125 OM4 (Serial NUMBER) (METRE MARK)

Fibers per Subunit, quantity 4

Total Fiber Count 4

Dimensions

 Cable Length
 2000 m | 6,561.68 ft

 Diameter Over Jacket
 6.4 mm | 0.252 in

Mechanical Specifications

Minimum Bend Radius, loaded129.5 mm | 5.098 inMinimum Bend Radius, unloaded80 mm | 3.15 inTensile Load, long term, maximum650 N | 146.126 lbfTensile Load, short term, maximum1250 N | 281.011 lbf

Optical Specifications



760254767 | C-004-CN-5K-M04BK/28G/GY/E

Fiber Type OM4, LazrSPEED®

Optical Specifications, Wavelength Specific

Attenuation, maximum 0.70 dB/km @ 1,300 nm | 3.50 dB/km @ 850 nm

Standards Compliance TIA-492AAAD (OM4)

Environmental Specifications

Operating Temperature $-20 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C} \left(-4 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F}\right)$

EN50575 CPR Cable EuroClass Fire Performance Eca

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Cable weight 48 kg/km | 32.255 lb/kft

Included Products

CS-5K-LT – LazrSPEED® 550 OM4 Bend-Insensitive Multimode

Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

