760254805 | C-024-DS-8W-MSUBK/GY/C



Indoor/Outdoor Low Smoke Zero Halogen, TeraSPEED® Tight Buffered Office DistributionFiber Fiber Optic Cable, 24 fiber, Singlemode OSla, black. Provides Rodent Resistance.

- · designed to offer flexibility, strength and compact construction for internal and interbuilding use
- non-metallic construction reinforced by E-glass yarns, which provide rodent resistance and higher tensile strength
- oversheathed with a ULSZH jacket meeting IEC fire performance requirements

Product Classification

 Regional Availability
 Asia | EMEA

 Portfolio
 CommScope®

Product Type Fiber indoor/outdoor cable

Product Series C-DS

General Specifications

Cable Type Tight buffer

Jacket ColorBlackJacket MarkingMetersJacket Marking MethodInkjet

Jacket Marking Text COMMSCOPE GB OPTICAL CABLE 760254805 24x9/125 OS1a ULSZH

[BATCH NUMBER] [METRE MARK]

Strength Members E-glass yarns

Total Fiber Count 24


Dimensions

Diameter Over Jacket 9.5 mm | 0.374 in

Representative Image



760254805 | C-024-DS-8W-MSUBK/GY/C



Mechanical Specifications

Minimum Bend Radius, loaded240 mm | 9.449 inMinimum Bend Radius, unloaded150 mm | 5.906 inTensile Load, short term, maximum2000 N | 449.618 lbfCable Crush Resistance, maximum20 N/mm | 114.203 lb/in

Optical Specifications

Fiber Type OS2

Optical Specifications, Wavelength Specific

Standards Compliance IEC 60794-1 | TIA-492CAAB (OS2)

Environmental Specifications

Installation temperature $-5 \,^{\circ}\text{C}$ to $+50 \,^{\circ}\text{C}$ (+23 $^{\circ}\text{F}$ to +122 $^{\circ}\text{F}$)

Operating Temperature $-20 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Storage Temperature $-20 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

EN50575 CPR Cable EuroClass Fire PerformanceCcaEN50575 CPR Cable EuroClass Smoke Ratings2EN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH)



760254805 | C-024-DS-8W-MSUBK/GY/C

Packaging and Weights

Cable weight 92 kg/km | 61.821 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

DB-8W-TB - LightScope® ZWP Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

