# URVLCLCGD

#### **Base Product**

### Ultra Low Loss (ULL) OM5 LC/UPC to LC/UPC Fanout Cable, 12-Fiber, LSZH & OFNR

#### Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Fiber array cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

### General Specifications

Color, boot A Lime green

Color, connector A Black

Color, boot B Lime green

Color, connector B Black

Construction Type Stranded

Furcation Color Lime green

Interface, Connector A LC/UPC

Interface, Connector B LC/UPC

Jacket Color Lime green

Fibers per Subunit, quantity 12

Total Fibers, quantity 12

#### Dimensions

Cable Assembly Length Range (m) 3 - 305


Cable Assembly Length Range (ft) 10 - 999

**Diameter Over Jacket** 3 mm | 0.118 in

## Ordering Tree



# **URVLCLCGD**



### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

**Fiber Mode** Multimode

**Fiber Type** OM5, LazrSPEED®

# **Environmental Specifications**

**Operating Temperature**  $-10 \,^{\circ}\text{C to} +60 \,^{\circ}\text{C (+14 °F to} +140 \,^{\circ}\text{F)}$ 

**Environmental Space**Dual Rated LSZH/OFNR | Indoor

### Regulatory Compliance/Certifications

Compliant

Agency Classification



### Included Products

760229039 – Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser Light Duty for MPO

Page 2 of 3

# URVLCLCGD

N-012-MP-5G-F30LM/D

Patchcords, 12 fiber, Multimode OM5, Gel-free, Feet jacket marking, Lime green jacket color, Dca Flame rating

