

# A7818473 | Optical Multiplexer, 8 channels



CWDM Fiber Optical Module, Mux, 1470-1610 nm, LC/PC, 8 channels

- Trade Agreements Act (TAA) compliant

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | CWDM module   |
| <b>Product Series</b>        | LGX   |

## General Specifications

|                      |                |
|----------------------|----------------|
| <b>Device Type</b>   | Plug-in module |
| <b>Functionality</b> | Multiplexing   |

## Dimensions

|               |                   |
|---------------|-------------------|
| <b>Height</b> | 29 mm   1.142 in  |
| <b>Width</b>  | 130 mm   5.118 in |
| <b>Depth</b>  | 185 mm   7.283 in |

## Packaging and Weights

|                       |                    |
|-----------------------|--------------------|
| <b>Height, packed</b> | 65 mm   2.559 in   |
| <b>Width, packed</b>  | 275 mm   10.827 in |
| <b>Depth, packed</b>  | 160 mm   6.299 in  |
| <b>Weight, gross</b>  | 0.5 kg   1.102 lb  |
| <b>Weight, net</b>    | 0.4 kg   0.882 lb  |