

BCU158-4M10M-7X



Grommet - Universal barrel cushion for 4-10 mm cables, accommodates up to quantity 7ea cables, for 1-5/8 in Standard or Click-on Hanger

Product Classification

Product Type	Grommet
Product Brand	HELIAX®
Ordering Note	CommScope® standard product (Global)

General Specifications

Adapter Type	Adapter
Cables per Hanger	7
Color	Black

Dimensions

Compatible Diameter, maximum	9.906 mm 0.39 in
Compatible Diameter, minimum	4.064 mm 0.16 in

Material Specifications

Material Type	EPDM rubber
----------------------	-------------

Environmental Specifications

Installation temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Height, packed	27.9 cm 10.984 in
Width, packed	30.5 cm 12.008 in
Length, packed	5.59 cm 2.201 in
Packaging quantity	10
Weight, gross	0.8 kg 1.764 lb

BCU158-4M10M-7X

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

