BCU158-4M10M-7X



Grommet - Universal barrel cushion for 4-10 mm cables, accommodates up to quantity 7ea cables, for 1-5/8 in Standard or Click-on Hanger

Product Classification

Product TypeGrommetProduct BrandHELIAX®

Ordering Note ANDREW® standard product (Global)

General Specifications

Adapter Type Adapter

Cables per Hanger 7

Color Black

Dimensions

Compatible Diameter, maximum9.906 mm | 0.39 inCompatible Diameter, minimum4.064 mm | 0.16 in

Material Specifications

Material Type EPDM rubber

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Packaging and Weights

 Height, packed
 27.9 cm | 10.984 in

 Width, packed
 30.5 cm | 12.008 in

 Length, packed
 5.59 cm | 2.201 in

Packaging quantity 10

Weight, gross 0.8 kg | 1.764 lb



BCU158-4M10M-7X

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

