

Outside Plant Fiber Optic Cable, armored, 6-fiber, SM, OS2, loose tube, gel-filled, 1000 m

Product Classification

Regional Availability	Asia
Portfolio	NETCONNECT®
Product Type	Fiber OSP cable

General Specifications

Armor Type	Corrugated steel
Cable Type	Loose tube
Fibers per Subunit, quantity	6
Jacket Color	Black
Subunit Type	Gel-filled
Total Fiber Count	6

Dimensions

Cable Length	1000 m 3,280.84 ft
Diameter Over Jacket	10.3 mm 0.406 in

Mechanical Specifications

Minimum Bend Radius, loaded	206 mm 8.11 in
Tensile Load, short term, maximum	2700 N 606.984 lbf

Optical Specifications

Fiber Type	OS2
-------------------	-----

Optical Specifications, Wavelength Specific

Standards Compliance	ANSI/TIA-568.A TIA-492CAAB (OS2)
-----------------------------	------------------------------------

Environmental Specifications

Installation temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

1-1427432-4

Packaging and Weights

Cable weight 108 kg/km | 72.573 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable