760255704 | BUDI-1S-T-A-16S216CS



BUDI™ Fiber Optic Wall mount Enclosure, 16 SC/APC adapters, single circuit FIST splice trays for 16 SMOUV splices

- Compact, wall mountable fiber enclosures for indoor and outdoor use
- Specifically designed for fast FTTH deployment and easy customer connection
- Available with splicing (FIST) and/or patching and/or splitter combinations
- Multiple and modular wrap around cable port sealing options

Product Classification

Regional Availability EMEA

PortfolioCommScope®Product TypeFiber wall box

Product Brand BUDI™
Product Series BUDI-1S

General Specifications

Functionality Patching | Splicing

Access Front
Enclosure Color Gray

Front Cover Type Snap-on cover

InterfaceSC/APCMountingWallPort, quantity16

Splice Tray Construction SC (Single circuit)

Splice Trays Included

Splice Trays Included, quantity 8
Splicing Capacity, maximum 16

Dimensions

 Height
 340 mm | 13.386 in

 Height, with cover
 420 mm | 16.535 in


 Width
 240 mm | 9.449 in

 Depth
 120 mm | 4.724 in



760255704 | BUDI-1S-T-A-16S216CS

Dimension Drawing



Material Specifications

Enclosure Material TypeLSZH thermoplastic

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor/Outdoor
Flammability Rating UL 94 V-0

Qualification Standards IEC 60529, IP54 | IEC 61753-1, category G

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted

Page 2 of 3

760255704 | BUDI-1S-T-A-16S216CS

UK-ROHS

Compliant/Exempted



