MC-FM3-24-278



Monopole Co-location 24" Stand-off Mount kit, 12 in to 50 in OD, includes 2-7/8" OD x 96" pipe

Product Classification

Product Type Stand-off mount

General Specifications

Mounting Monopole, 304.8–1270 mm (12–50 in) OD

Pipe, quantity 12
Sectors, quantity 3

Dimensions

Height 2,438.4 mm | 96 in

Face Width 0 m | 0 ft

 Width
 279.4 mm | 11 in

 Length
 609.6 mm | 24 in

 Pipe Length
 2,438.4 mm | 96 in

 Mounting Diameter, maximum
 1270 mm | 50 in

 Mounting Diameter, minimum
 304.8 mm | 12 in

 Pipe Outer Diameter
 73.025 mm | 2.875 in

 Stand-off Distance
 609.6 mm | 24 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222-G

Packaging and Weights

Included Pipe mounts | Plain end pipes (3) | Ring mount | Stand-off arms

Packaging quantity 1

ANDREW® an Amphenol company

MC-FM3-24-278

Weight, net

229.835 kg | 506.7 lb

