


A-VF1-SOXXG

Base Product



Cheshire Cabinet with rails and brackets fitted to accommodate up to 12 Samsung Radios

- Includes fans with controller
- Supplied with 20 meter fan controller power cable
- Supplied with 20 meter alarm cable
- Contains two GPS windows (blanked and plastic covered)

Product Classification

Regional Availability	EMEA
Product Type	Outdoor cabinet

General Specifications


Access	Double door
Accessories	Cable plate External alarm connection Hangers In-ground root Plinth
Cabinet Type	Combiner cabinet Radio cabinet
Cable Entry Location	Bottom
Color	Green (RAL 6009) Light Gray (RAL 7035) Others available at additional cost
Cooling	175 mm fan (2)
Door Security	Internal door contact Swing handle with European profile cylinder
Door Type, front	Key lock (includedI) Non-removable
Door, quantity	2
Front Door Type	Single hinged
Lock Type	Key lock
Mounting	In-ground root Plinth
Radios Included	None

Dimensions

Height	1,721.866 mm 67.79 in
Width	1,899.92 mm 74.8 in
Depth	599.948 mm 23.62 in

Dimension Drawing

A-VF1-S0XXG



Material Specifications

Finish	Powder coated
Material Type	Galvanized steel

Environmental Specifications

Qualification Standards	IP33
--------------------------------	------

Packaging and Weights

Weight, net	299.997 kg 661.38 lb
--------------------	------------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system