UJGMXUCSF

Base Product



Ultra Low Loss (ULL) Singlemode MPO12 (Pinned) to Unconnectorized, Fiber Trunk Cable Assembly, 24-Fiber, Dual Rated LSZH/Riser Cca

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

Product Type Fiber trunk cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

General Specifications

Color, boot A Black
Color, connector A Green

Construction Type Rollable ribbon

Furcation Color Yellow

Interface, Connector A MPO-12/APC Male

Jacket Color Black

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 24

Dimensions

Breakout Length 33 in


Cable Assembly Length Range (m) 3 - 999

Cable Assembly Length Range (ft) 10 - 999

Ordering Tree



UJGMXUCSF



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Singlemode

G.657.A2, TeraSPEED® **Fiber Type**

Environmental Specifications

-10 °C to +60 °C (+14 °F to +140 °F) **Operating Temperature**

Environmental Space Dual Rated LSZH/Riser | Indoor/Outdoor

Included Products

Fiber indoor/outdoor cable, OFNR/LSZH Riser Rollable Ribbon Dual Rated Backbone, 24 fiber, 760256411 Z-024-MP-RR-F12BK/8G1/99N /C

Singlemode G.657.A2/B2, Feet jacket marking, Black jacket color, Cca flame rating

MPO12, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 3mm 860638317