

UGGQXUCZ8

Base Product



Hybrid Ultra Low Loss (ULL) Singlemode G.657.A2 MPO8 (Pinned) to Unconnectorized , 4 Pair 16AWG Constellation Trunk Cable Assembly, 8-Fiber, Plenum

Product Classification

Regional Availability	Asia Australia/New Zealand China Europe India Latin America Middle East/Africa North America
Portfolio	CommScope®
Product Type	Hybrid cable assembly 4-pair
Product Brand	SYSTIMAX ULL
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

General Specifications


Conductor Capacitance	75.459 pF/m 23 pF/ft
Conductor Resistance	14.698 ohms/km 4.48 ohms/kft
Conductor Type	16 AWG Stranded
Conductors, quantity	8
Conductor Pairs, quantity	4
Connector A, quantity	1
Color, boot A	Gray
Color, connector A	Green
Construction Type	Hybrid standard trunk
Furcation Color	Yellow
Interface, Connector A	MPO-08/APC Male
Jacket Color	Yellow
Polarity	Method B Enhanced (ULL)
Fibers per Subunit, quantity	8
Total Fibers, quantity	8

Dimensions


UGGQXUCZ8

Breakout Length	24 in 72 in
Cable Assembly Length Range (m)	10 – 999
Cable Assembly Length Range (ft)	33 – 999

Dimension Drawing



Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 ° 4.40 lb @ 90 °
--	---------------------------------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2, TeraSPEED®

UGGQXUCZ8

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Indoor Plenum
Qualification Standards	GR-3108 class 4

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Included Products

860659022	– MPO-08, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 2mm
-----------	--