## MUK-MSK6 | BACK TO BACK CROSSOVER



Dual Cross Over Plate, Mounts (2) 3-1/2" to 4-1/2" Pipes to 4" or 6" Square Tube

Product Classifica	ation	
Product Type		Clamp plate
General Specifica	tions	
Mounting		Crossover plate
Dimensions		
Mounting Diameter 2, maximum		152.4 mm   6 in
Mounting Diameter 2, minimum		101.6 mm   4 in
Mounting Diameter, maximum		114.3 mm   4.5 in
Mounting Diameter, minimum		88.9 mm   3.5 in
Material Specifica	ations	
Material Type		Hot dip galvanized steel
<b>F</b>		
Environmental Specifications		
EPA with 1/2 in (12 mm) radial ice		ft²
Packaging and Weights		
Included		Plates   U-bolts
Packaging quantity		1
Regulatory Compliance/Certifications		
Agency	Classification	
CHINA-ROHS	Above maximum concentration value	
ROHS	Compliant/Exempted	

Compliant/Exempted



Page 1 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

## MUK-MSK6 | BACK TO BACK CROSSOVER

## \* Footnotes

EPA with 1/2 in (12 mm) radial ice EPA-Effective Projected Area

Page 2 of 2



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025