


MUK-MSK14 | UNIVERSAL ADJUSTABLE CROSSOVER



Universal Crossover Plate, Round - joins range of 2-3/8 up to to 3-1/2 in OD round members

Product Classification

Product Type Clamp plate

General Specifications

Mounting Crossover plate

Dimensions

Height 139.7 mm | 5.5 in

Width 139.7 mm | 5.5 in

Length 266.7 mm | 10.5 in

Mounting Diameter 2, maximum 88.9 mm | 3.5 in

Mounting Diameter 2, minimum 60.96 mm | 2.4 in

Mounting Diameter, maximum 88.9 mm | 3.5 in

Mounting Diameter, minimum 60.96 mm | 2.4 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Hardware | Plates

Packaging quantity 1

Weight, net 5 kg | 11.023 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

MUK-MSK14 | UNIVERSAL ADJUSTABLE CROSSOVER

UK-ROHS

Compliant

