

760255053 | PPL-SP-24LC-SM-PT-BEU



Propel Splice Cassette, 24LC/UPC with internal shutters, OS2 with 250 μ m single fiber pigtails, Method B Enhanced ULL

- Can be installed and removed from front or rear of panel
- This component requires 6 of the 12 lanes on the Propel Panel blade
- Compatible with either 250 μ m or 900 μ m incoming fiber

Recommended for use with 24f subunit cable

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cassette with pigtails
Product Brand	Propel
Product Series	PPL

General Specifications

Color, front	Blue
Interface, front	LC/UPC
Interface, rear	Stranded pigtail
Polarity	Method B Enhanced (ULL)
Shuttered	Yes
Total Fibers, quantity	24

Dimensions

Height	67.31 mm 2.65 in
Width	196.012 mm 7.717 in

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2
Insertion Loss, maximum	0.25 dB

Environmental Specifications

760255053 | PPL-SP-24LC-SM-PT-BEU

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	UL
Packaging and Weights	
Included	Single Fusion Splice Protection Sleeves
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant



Included Products

103897-000	–	SMOUV Fiber Optic Splice Heat Shrink Protective Sleeve for Single Fusion (See Specs for
SMOUV-1120-02		packaging size and MOQ)