

## LMR-195 Jumper with interface types QMA Male and QMA Male, 1 m



### Product Classification

**Product Type** Coaxial wireless cable

### General Specifications

**Body Style, Connector A** Straight

**Body Style, Connector B** Straight

**Interface, Connector A** QMA Male

**Interface, Connector B** QMA Male

**Specification Sheet Revision Level** A

### Dimensions

**Length** 1 m | 3.281 ft

**Nominal Size** 0.195 in

### VSWR

/Return

Loss

Frequency Band	VSWR	Return Loss (dB)	Insertion Loss (dB)	VSWR, typical	Return Loss, typical (dB)	Insertion Loss, typical (dB)
0–3000 MHz	1.222	20	1.2	1.184	21.5	1.05

### Mechanical Specifications

**Minimum Bend Radius, multiple Bends** 50.8 mm | 2 in

**Minimum Bend Radius, single Bend** 12.7 mm | 0.5 in

### Environmental Specifications

**Environmental Space** Low Smoke Zero Halogen (LSZH)

### Packaging and Weights

# 7855826

---

**Weight, gross** 0.06 kg | 0.132 lb

**Weight, net** 0.05 kg | 0.11 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

