

LMR-195 Jumper with interface types QMA Male and QMA Male, 2 m



Product Classification

Product Type Coaxial wireless cable

General Specifications

Body Style, Connector A Straight

Body Style, Connector B Straight

Interface, Connector A QMA Male

Interface, Connector B QMA Male

Specification Sheet Revision Level A

Dimensions

Length 2 m | 6.562 ft

Nominal Size 0.195 in

VSWR

/Return

Loss

Frequency Band	VSWR	Return Loss (dB)	Insertion Loss (dB)	VSWR, typical	Return Loss, typical (dB)	Insertion Loss, typical (dB)
0–3000 MHz	1.222	20	2.05	1.184	21.5	1.9

Mechanical Specifications

Minimum Bend Radius, multiple Bends 50.8 mm | 2 in

Minimum Bend Radius, single Bend 12.7 mm | 0.5 in

Environmental Specifications

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

7855827

Weight, gross 0.1 kg | 0.22 lb

Weight, net 0.09 kg | 0.198 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

