

## LMR-195 Jumper with interface types N Male and SMA Male, 3 m



### Product Classification

**Product Type** Coaxial wireless cable

### General Specifications

**Body Style, Connector A** Straight

**Body Style, Connector B** Straight

**Interface, Connector A** N Male

**Interface, Connector B** SMA Male

**Specification Sheet Revision Level** A

### Dimensions

**Length** 3 m | 9.843 ft

**Nominal Size** 0.195 in

### VSWR

### /Return

### Loss

Frequency Band	VSWR	Return Loss (dB)	Insertion Loss (dB)	VSWR, typical	Return Loss, typical (dB)	Insertion Loss, typical (dB)
0–3000 MHz	1.222	20	1.8	1.184	21.5	1.61

### Mechanical Specifications

**Minimum Bend Radius, multiple Bends** 63.5 mm | 2.5 in

**Minimum Bend Radius, single Bend** 19.1 mm | 0.752 in

### Packaging and Weights

**Weight, gross** 0.21 kg | 0.463 lb

**Weight, net** 0.19 kg | 0.419 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

