

# MTC4107S

---

Four-Sector Double T-Arm Monopole Mount, Includes (2) Ring Mounts for 10"-30" OD Monopole, 6 ft x 3-1/2" OD face pipes, (12) 2-3/8" OD x 96" Antenna Pipes

## Product Classification

**Product Type** Monopole T-frame kit

## General Specifications

**Mounting** Monopole, 254–762 mm (10–30 in) OD

**Pipe, quantity** 12

**Sectors, quantity** 4

## Dimensions

**Height** 2,438.4 mm | 96 in

**Face Width** 1.829 m | 6 ft

**Width** 1,828.8 mm | 72 in

**Pipe Length** 2,438.4 mm | 96 in

**Face Support Pipe Diameter** 88.9 mm | 3.5 in

**Mounting Diameter, maximum** 762 mm | 30 in

**Mounting Diameter, minimum** 254 mm | 10 in

**Pipe Outer Diameter** 60.325 mm | 2.375 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** For Specifications, please contact [steelproducts@commscope.com](mailto:steelproducts@commscope.com) or call 800-255-1479

**Wind Rating Test Method** TIA/EIA-222-G

## Packaging and Weights

**Included** Frame | Pipe mounts | Plain end pipes | Ring mounts (2)

**Packaging quantity** 1

**Weight, net** 897.024 kg | 1,977.6 lb

# MTC4107S

---

\* Footnotes

**Wind Rating**

BWS—Base Wind Speed; FBC—Florida Building Code