



FiberGuide® 4in Express Exit Left and Right Restraining Brackets, Kit of 10, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Accessory
Product Brand	FiberGuide®
Product Series	FGS

General Specifications

Product Feature	Round
Color	Black
Orientation	Horizontal
Section Type	Accessory

Dimensions

Width	89.662 mm 3.53 in
System Dimensions	102 mm x 102 mm (4 in x 4 in)

Ordering Tree

FGSB-ACC002

9

FGS

B

-

MEXP

-

10

A/B/F

Section Color

9	empty	yellow
	B	black

Section Size

10	A/B/F	4 x 4/6/12 in, with 2 x 2 in exit
	E-A/B/F	4 x 4/6/12 in, with 4 x 4 in exit
	F-F/H-NC	4 x 12/18/24 in, with 4 x 12 in exit, no cover
	G-A/B/F	4 x 4/6/12 in, with 4 x 6 in exit
	LP-A/B/F	4 x 4/6/12 in, with 2 x 2 in exit, low profile
	LP-CA	4 x 4/6/12 in, with 2 x 4 in exit, low profile
	LP-G	2 x 6 in, with 2 x 2 in exit, low profile
	GS-ABF-NC	4 x 4/6/12 in, with 4 x 6 in exit, no cover
	CV	cover
NC	no cover	

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0

Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

Included Hardware

Packaging quantity 10

Weight, net 0.568 kg | 1.252 lb