



Monopole Hoisting Grip Anchor, for Monopoles 10"-35" OD

Engineered attachment anchor point solution for 10" to 35" diameter monopoles to accommodate and support cable via the wire mesh grip.

- MAXIMUM LOAD PER EYEBOLT = 1000 LBS
- MAXIMUM LOAD PER MOUNT = 3000 LBS
- REVIEWED FOR USE WITH A MINIMUM POLE DIAMETER OF 10" WITH WALL THICKNESS OF 3/16" AND A YIELD STRENGTH OF 36 KSI. FOR USE ON THINNER MATERIAL REQUIRES ADDITIONAL ENGINEERING REVIEW

Supports all cables types anchored with a hoisting grip including Hybrid cable.
860669616-1035-T Mounting Kit for Top of Monopole ordered separately

- Competent person to make determination of usage on the structure

Product Classification

Portfolio	CommScope®
Product Type	Hoisting Grip Anchor
Warranty	One year

General Specifications

Cable Runs, quantity	3
Mounting	Round member

Dimensions

Height	101.6 mm 4 in
Mounting Diameter, maximum	889 mm 35 in
Mounting Diameter, minimum	254 mm 10 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

860669616-1035

Packaging and Weights

Included	Mount Threaded rod
Packaging quantity	1
Weight, net	22.45 kg 49.494 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



* Footnotes

Warranty	For more information, please consult our Product Warranty guidelines
-----------------	--