

# MTC4074M6996

---

Three-Sector Double T-Arm Monopole Mount, Includes (2) Ring Mounts for 15"-50" OD Monopole, 6 ft x 3-1/2" OD face pipes, (9) 2-3/8" OD x 96" Antenna Pipes

## Product Classification

**Product Type** Monopole T-frame kit

## General Specifications

**Mounting** Monopole, 381–1270 mm (15–50 in) OD

**Pipe, quantity** 9

**Sectors, quantity** 4

## Dimensions

**Height** 2,438.4 mm | 96 in

**Face Width** 1.829 m | 6 ft

**Width** 1,828.8 mm | 72 in

**Pipe Length** 2,438.4 mm | 96 in

**Face Support Pipe Diameter** 88.9 mm | 3.5 in

**Mounting Diameter, maximum** 1,270 mm | 50 in

**Mounting Diameter, minimum** 381 mm | 15 in

**Pipe Outer Diameter** 60.325 mm | 2.375 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** For Specifications, please contact [steelproducts@commscope.com](mailto:steelproducts@commscope.com) or call 800-255-1479

**Wind Rating Test Method** TIA/EIA-222-G

## Packaging and Weights

**Included** Frame | Pipe mounts | Plain end pipes | Ring mounts (2)

**Packaging quantity** 1

**Weight, net** 759.445 kg | 1,674.29 lb

# MTC4074M6996

---

\* Footnotes

**Wind Rating**                    BWS—Base Wind Speed; FBC—Florida Building Code