
# 760248392 | MPA-PCLCJ50006M-NS



MPO Fanout Cable, polarity A, 12 fiber MPO (pinned) to LC duplex, Plenum 3mm SM, 6m, with 36" breakout

## **Product Classification**

Regional Availability Latin America | North America

Portfolio CommScope®

**Product Type** Fiber fanout cable assembly

Product Brand MPOptimate®

Product Series MPA

## General Specifications

Connector A, quantity 1

Color, boot ABlackColor, connector AGreenConnector B, quantity12Color, boot BBlueColor, connector BBlue

**Construction Type** Plug-and-play, array cord

Interface, Connector A MPO-12/UPC Male

Interface Feature, connector A Pinned
Interface, Connector B LC/UPC

Jacket Color Yellow

**Total Fibers, quantity** 12

**Dimensions** 

**Cord Length** 6 m | 19.685 ft

**Optical Specifications** 

Fiber Mode Singlemode

Fiber Type OS2

COMMSCOPE®

#### 760248392 MPA-PCLCJ50006M-NS

# **Environmental Specifications**

**Environmental Space** Plenum

Packaging and Weights

**Packaging quantity** 

Regulatory Compliance/Certifications

Classification **Agency** 

CHINA-ROHS Below maximum concentration value

**ROHS** Compliant **UK-ROHS** Compliant



### Included Products

Fiber indoor cable, Plenum for MPO Light Duty Patchcords, 12 fiber, Singlemode G.657.A2/B2, 760237964 P-012-MP-8G1-F30YL

Feet jacket marking, Yellow jacket color

LC/UPC Connector, Singlemode, Blue, Short Boot 860637435

MPO12, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 3mm 860638317