



HTB2 Home Termination Box with Patch capacity for 1 SC/APC connection and splice capacity up to 4 splices, SC/APC Adapter included, no pigtails included

- SC/UPC, SC/APC, LC/UPC and LC/APC connector versions

Product Classification

Regional Availability	India Latin America
Product Type	Fiber wall box
Product Series	HTB2

General Specifications

Functionality	Patching Splicing
Adapters, quantity	1
Cable Ports, quantity	7
Cable Type	Indoor - Ribbon
Color	White
Distribution Type	1 port
Front Cover Type	Screw-on
Interface	SC/APC
Lock Type	Standard screw
Mounting	Wall mount
Patch Cord Routing	Downward
Patching Capacity, maximum	2
Pigtails Included, quantity	0
Port Color	Green
Port, quantity	1
Splicing Capacity, maximum	4

Dimensions

Height	86 mm 3.386 in
Width	86 mm 3.386 in

760250531 | HTB2-1F-SCAP-A1-P0-EXP

Depth 22 mm | 0.866 in

Material Specifications

Material Type Acrylnitril Butadien Styrol (ABS)

Environmental Specifications

Operating Temperature -5 °C to +55 °C (+23 °F to +131 °F)

Environmental Space Indoor

Flammability Rating UL 94 V-0

Qualification Standards IEC 60529, IP40

Packaging and Weights

Packaging Type Box

Weight, net 0.05 kg | 0.11 lb