


MCG22HD-14M-B



G22HD High Capacity 3-Sector Monopole Frame with 2 7/8in OD x 14.5 ft face - Base Kit Only. No antenna pipes

Product Classification

Product Type	High capacity monopole sector frame
Product Series	G2

General Specifications

Mounting	Monopole, 381–1270 mm (15–50 in) OD
Pipe, quantity	0
Sectors, quantity	3

Dimensions

Face Width	4.42 m 14.5 ft
Face Support Pipe Diameter	73.025 mm 2.875 in
Mounting Diameter, maximum	1270 mm 50 in
Mounting Diameter, minimum	381 mm 15 in
Stand-off Distance	1,041.4 mm 41 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating	For Specifications, please contact steelproducts@commscope.com or call 800-255-1479
Wind Rating Test Method	TIA/EIA-222

Packaging and Weights

Included	Ring mounts (2) Sector frames (3) Stiff arm
Packaging quantity	1

Regulatory Compliance/Certifications

MCG22HD-14M-B

Agency

CHINA-ROHS

ROHS

UK-ROHS

**Classification**

Above maximum concentration value

Compliant/Exempted

Compliant/Exempted

* Footnotes

Wind Rating

BWS—Base Wind Speed; FBC—Florida Building Code