MCG22HDX-14M-B



G22HDX High Capacity 3-Sector Monopole Frame with 2 7/8in OD x 14.5 ft face. Base Kit Only. No antenna pipes.

Product Classification

Product Type High capacity monopole sector frame

Product Series G2

General Specifications

Mounting Monopole, 381–1270 mm (15–50 in) OD

Pipe, quantity 0
Sectors, quantity 3

Dimensions

Face Width $4.42 \text{ m} \mid 14.5 \text{ ft}$

Face Support Pipe Diameter 73.025 mm | 2.875 in

Mounting Diameter, maximum1270 mm | 50 inMounting Diameter, minimum381 mm | 15 inStand-off Distance1,066.8 mm | 42 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Ring mounts (2) | Sector frames (3) | Stiff arm

Packaging quantity 1

Regulatory Compliance/Certifications



MCG22HDX-14M-B

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

