

760255044 | PPL-SP-12LC-OM4-PT-BEU



Propel Multimode Splice Cassette, 12LC with internal shutters, OM4 single fiber pigtails, Method B Enhanced ULL

- Can be installed and removed from front or rear of panel
- This component requires 3 of the 12 lanes on the Propel Panel blade
- Compatible with either 250 μm or 900 μm incoming fiber

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cassette with pigtails
Product Brand	Propel
Product Series	PPL

General Specifications

Color, front	Aqua
Interface, front	LC/UPC
Interface, rear	Stranded pigtail
Polarity	Method B Enhanced (ULL)
Shuttered	Yes
Total Fibers, quantity	12

Dimensions

Height	67.31 mm 2.65 in
Width	97.993 mm 3.858 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	G.657.A2
Insertion Loss, maximum	0.15 dB

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
--------------------------------	---------------------------

760255044 | PPL-SP-12LC-OM4-PT-BEU

Safety Standard UL

Packaging and Weights

Included Single Fusion Splice Protection Sleeves

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

- 103897-000 – SMOUV Fiber Optic Splice Heat Shrink Protective Sleeve for Single Fusion (See Specs for
SMOUV-1120-02 packaging size and MOQ)