## 760255057 | PPL-SP-24LC-0M4-RPT-BEU



Propel Multimode Splice Cassette, 24LC with internal shutters, OM4 ribbon fiber pigtail, Method B Enhanced ULL

- Can be installed and removed from front or rear of panel
- This component requires 6 of the 12 lanes on the Propel Panel blade

Recommended for use with 24f subunit cable

#### Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

**Product Type** Fiber cassette with ribbon pigtail

Product Brand Propel
Product Series PPL

#### General Specifications

Color, front Aqua
Interface, front LC/UPC

Interface, rear Ribbon pigtail

Polarity Method B Enhanced (ULL)

Shuttered Yes
Total Fibers, quantity 24

**Dimensions** 

 Height
 67.31 mm | 2.65 in

 Width
 196.012 mm | 7.717 in

### **Optical Specifications**

Fiber ModeMultimodeFiber TypeG.657.A2Insertion Loss, maximum0.15 dB

### **Environmental Specifications**

**Qualification Standards** IEC 61753-1 | TIA-568.3-D

Page 1 of 2

# 760255057 | PPL-SP-24LC-0M4-RPT-BEU

Safety Standard

Packaging and Weights

**Included** Mass Fusion Splice Protection Sleeves

UL

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### Included Products

FST-ACC006 – Mass Fusion Splice Protector (See Specs for packaging size and

MOQ)

