



Propel Multimode Field Term Cassette, 24LC with internal shutters, no fiber

- Can be installed and removed from front or rear of panel
- This component requires 6 of the 12 lanes on the Propel Panel blade

Recommended for use with 24f subunit cable

Product Classification

Portfolio	CommScope®
Product Type	Fiber cassette
Product Brand	Propel
Product Series	PPL

General Specifications

Color, front	Aqua
Interface, front	LC/UPC
Interface, rear	No pigtail
Shuttered	Yes
Total Fibers, quantity	24

Dimensions

Height	67.31 mm 2.65 in
Width	196.012 mm 7.717 in

Optical Specifications

Fiber Mode	Multimode
-------------------	-----------

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	UL

Packaging and Weights

Included	Single Fusion Splice Protection Sleeves
-----------------	---

760255065 | PPL-FT-24LC-OM4-00-000

Packaging quantity 1