

760255068 | PPL-SP-4MPO12-SM-RPT-BEU



Propel Singlemode Splice Cassette, 4 MPO12 non-pinned with internal shutters, OS2 ribbon fiber pigtail, Method B Enhanced ULL

- Can be installed and removed from front or rear of panel
- This component requires 3 of the 12 lanes on the Propel Panel blade

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cassette with ribbon pigtail
Product Brand	Propel
Product Series	PPL

General Specifications

Color, front	Gray
Interface, front	MPO Unpinned
Interface, rear	Ribbon pigtail
Polarity	Method B Enhanced (ULL)
Shuttered	Yes
Total Fibers, quantity	48

Dimensions

Height	67.31 mm 2.65 in
Width	97.993 mm 3.858 in

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2
Insertion Loss, maximum	0.25 dB

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	c-UL-us

Packaging and Weights

Included	Mass Fusion Splice Protection Sleeves
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

