

# 760255081 | PPL-SP-24LC-SM-PT-AS



Propel Singlemode Splice Cassette, 24LC/UPC with internal shutters, 250  $\mu$ m OS2 single fiber pigtails, pairs straight ULL

- Can be installed and removed from front or rear of panel
- This component requires 6 of the 12 lanes on the Propel Panel blade
- Compatible with either 250  $\mu$ m or 900  $\mu$ m incoming fiber

Recommended for use with 24f subunit cable

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber cassette with pigtails
Product Brand	Propel
Product Series	PPL

## General Specifications

Color, front	Blue
Interface, front	LC/UPC
Interface, rear	Stranded pigtail
Polarity	Pairs, straight
Shuttered	Yes
Total Fibers, quantity	24

## Dimensions

Height	67.31 mm   2.65 in
Width	196.012 mm   7.717 in

## Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2
Insertion Loss, maximum	0.25 dB

## Environmental Specifications

Qualification Standards	IEC 61753-1   TIA-568.3-D
Safety Standard	UL
Packaging and Weights	
Included	Mass Fusion Splice Protection Sleeves
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant

