



Propel Multimode Splice Cassette, 24LC with internal shutters, OM5 single fiber pigtails, pairs straight ULL

- Can be installed and removed from front or rear of panel
- This component requires 6 of the 12 lanes on the Propel Panel blade
- Compatible with either 250 µm or 900 µm incoming fiber

Recommended for use with 24f subunit cable

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cassette with pigtails
Product Brand	Propel
Product Series	PPL

General Specifications

Color, front	Lime green
Interface, front	LC/UPC
Interface, rear	Stranded pigtail
Polarity	Pairs, straight
Shuttered	Yes
Total Fibers, quantity	24

Dimensions

Height	67.31 mm 2.65 in
Width	196.012 mm 7.717 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	G.657.A2
Insertion Loss, maximum	0.15 dB

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	UL

Packaging and Weights

Included	Single Fusion Splice Protection Sleeves
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

